


Cryostat development: Publicly funded basic research


Non-metallic cryostats for extreme requirements




Supported by:
 Federal Ministry
for Economic Affairs
and Energy

on the basis of a decision
by the German Bundestag


Universal measuring bridge



Resistance – Temperature Bridge



HTS-interception multiplexer with
4x temperature and 4x voltage taps




Multiplexer inside a
SubD25 plug

- Evaluation of new material-combinations
- Glass and carbon fiber composites based on epoxy resins
- Joining technology
- Stability at high temperatures
- Increased stability


- Sensor AC excitation < 1 nW possible
- Direct resistance comparison to reference resistor or voltage (0.01 %)
- Multiplexers for the connection of up to 80 sensors with ext. interface
- Calibration data for each sensor (3x8 poly)
- Data connection via USB / RS485 bus / SD-card
- Display: LC or TFT with touchscreen
- Housing: Hand held, industry PS or metal, integratable, size: 150 x 100 x 45 mm³

Development of innovative magnetic low-noise helium cryostats

- No LN₂ – Reservoir necessary!
- Liquid He volume: 12 liters; Operation time 4 days without refill
- Evaporation rate ≤ 3 liter LHe per day
- 0.1 W standby heat load; Helium leakage rate 4×10⁻⁹ mbar l/s



- Minimized electromagnetic interaction
e.g. use of non-conductive MLI
- Extremely low magnetic noise
- Fast charge with thermo-syphon



Supported by:
 Federal Ministry
for Economic Affairs
and Energy

on the basis of a decision
by the German Bundestag

Magnetic noise measurements (at PTB Berlin)